




PREMIUM SERIES ADJUSTABLE PEDESTALS & AUXILIARY PARTS

pedexon
Product Data Sheet

- Plastic raised floor pedestals are used in trafficable and non-trafficable flat roofs, in order to reach the desired final level and to remove the slope differences. The purpose here is to make the top coat flooring without placing a protection alum on the insulation and to establish a consistent drainage system by means of the open joint gaps of the floor cover. At the same time, these pedestals establishing a system, which is open to interference any time, are also quite durable with their avg. bearing capacity of 2000 lbs. Contains more than 30% post-industrial recycled material.
- Multiple auxiliary parts can be applied the same unit. Coupler must be used when the system is longer than 7 inches. There is no need coupler until 7 inches. Code: T-C
- Slope corrector: working with the bottom of the pedestal, avoids pressures of drain slopes on plates. Slope corrector can tolerate an degree several angles. Alternatives of 1 % and 2% are available. Code: T-SC
- Made of natural rubber material, the orthopedic floor pad helps to absorb all impact vibrations caused by bumpy surfaces. Thickness is 0.2 Code: T-P
- Pedestal bracing system for additional stability and heights over 24 inches. Impervious to water, mold and freeze/ thaw cycles.



PRODUCT DETAILS

ADJUSTABLE PEDESTAL (T-A)
Recycled-Polypropylene
Bearing Capacity: 2000 lbs




COUPLER (T-C)
Recycled-Polypropylene
Height: 2 1/2" - 4"



FIXED JOINT STRIPS (T-ST)
Recycled-Polypropylene



FIXED JOINT STRIPS (T-SF)
Recycled-Polypropylene
Thickness : 1/8"




PLUS SHAPE FORMED JOINT STRIPS (T-SP)
Recycled-Polypropylene
Thickness : 1/8"



LOCK (T-L)
Recycled-Polypropylene



SLOPE CORRECTOR (T-SC)
Recycled-Polypropylene
Grade: %1 and %2




CARCASS ASSEMBLY EQUIPMENT (T-AW)
Recycled-Polypropylene
Thickness : 1/8"




DIAGONAL CARCASS ASSEMBLY UNIT (T-AR)
(Rotatable self-axis)
Recycled-Polypropylene



ORTHOPEDICS FLOOR PAD
Natural Rubber (T-P)
Thickness : 1/5"



FIXED JOINT STRIPS (T-ST)
Recycled-Polypropylene
Thickness : 1/16" to 1/4



SHIMS (T-S)
EPDM
Thickness : 0.05" to 0.08"

